

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-833 3-4 DAYS



1



€2.445,00

ADD TO CART

Qty 1+

€2.445,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Input Voltage (V):
24

Model Number:
LFV3-G-30X60SW

Dimensions (mm):
W 68 mm x D 60 mm x H 35 mm

Weight (g):
165

Power Consumption (W): 12
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-733 China: #66-855
Active Area (mm): 30 mm x 60 mm
Color Temperature (K): 7000
Type of Illumination: LED Illuminator
Manufacturer: CCS
Geometry: Coaxial Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View