

3.25" x 4.00", 3.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-113** ☐ In Stock

-

1

+

€61,50

ADD TO CART

Qty 1-10

€61,50

Qty 11+

€54,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
76.20

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 3.25 x 4.0
Dimensions (mm): 82.55 x 101.6
Effective Focal Length EFL (inches): 3.00
Effective Size (inches): 3.0 x 4.0
Groove Density (grooves/inch): 80.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Transmission (%): 85 (Typical)
Thickness Tolerance (inches): ±0.020

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View