

3.25" x 4.00", 6.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-114** 6 In Stock

-

1

+

€65⁴¹

ADD TO CART

Volume Pricing	
Qty 1-10	€65,41 each
Qty 11-49	€58,71 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

Fresnel Lens

Physical & Mechanical Properties

0.06	Center Thickness CT (inches):
±0.05	Dimensional Tolerance (inches):
3.25 x 4.0	Dimensions (inches):
82.55 x 101.6	Dimensions (mm):
3.0 x 4.0	Effective Size (inches):
±0.020	Thickness Tolerance (inches):
Optical Properties	
152.40	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
6.00	Effective Focal Length EFL (inches):
65.00	Groove Density (grooves/inch):
1.49	Index of Refraction (n _d):
85 (Typical)	Transmission (%):
Environmental & Durability Factors	
80 (Maximum)	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

PRODUCT DETAILS

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

TECHNICAL INFORMATION

