

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-201 3-4 DAYS

[Other Coating Options](#)



1



€60,00

ADD TO CART

Qty 1-10

€60,00

Qty 11+

€54,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
34.90 +0.0/-0.2

Effective Focal Length EFL (mm):
21.60

Numerical Aperture NA:
0.81

Back Focal Length BFL (mm): 11
Substrate: ☐ H-K51
Focal Length Tolerance (%): ±5
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 31.41
Edge Thickness ET (mm): 2.91
Center Thickness CT (mm): 19.00 ±0.30
f/#: 0.62
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 34.9
Radius R₂ (mm): 71.12
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant