

TECHSPEC[®] 35mm - 60mm Length, T-Mount Fine Focus Tube



Stock #52-300 5 In Stock

-

1

+

€117⁴²

ADD TO CART

Volume Pricing	
Qty 1-4	€117,42 each
Qty 5-9	€103,93 each
Qty 10-25	€96,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Fine Focus Tube

Type:

Extension Tube (Adjustable)		Function:
Physical & Mechanical Properties		
35.0 - 60.0	Extension Length (mm):	
48.0	Outer Diameter (mm):	
33.0	Clear Aperture CA (mm):	
Threading & Mounting		
M33 x0.5	Barrel Thread:	
T-Mount	Thread Type:	
Regulatory Compliance		
Compliant	RoHS 2015:	
View	Certificate of Conformance:	
Compliant	Reach 235:	

PRODUCT DETAILS

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

Note: Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

TECHNICAL INFORMATION

