

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

355 & 332nm, 8-12mm Dia. Input Beam, Focal Flat Top Beam Shaper | Focal πShaper_NUV_Q 10

See More by [AdlOptica](#)



Stock #12-240 3-4 DAYS



1



€3.356,00

ADD TO CART

Qty 1-4

€3.356,00

Qty 5+

€3.019,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
20

Design Wavelength DWL (nm): 355, 532
Diameter (mm): 42.00
Model Number: πShaper_NUV_Q10
Length (mm): 29.00
Transmission (%): >99
Type: Beam Shaper
Weight (g): 50
Wavelength Range (nm): 335 - 560
Input Beam Diameter, 1/e² (mm): 8 - 12
Maximum Input Power, CW (kW): 0.2
Inner Thread: M30 x 0.75
Outer Thread: M30 x 0.75
Compatible Adapter: #12-322
Input Beam Mode: TEM ₀₀
Typical Input Beam Mode Quality, M²: <1.5
Input Beam Divergence (mrad): ±20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant