

355nm CWL, 25.4mm Dia., OD 6 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #15-400 3-4 DAYS

- 1 +

€1.865,00

ADD TO CART

Qty 1-9
€1.865,00
Qty 10+
€1.670,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.20

Angle of Incidence (°):

0
Optical Density OD (Average): 6.00
Clear Aperture CA (mm): 21.30
Center Wavelength CWL (nm): 354.78
Full Width-Half Max FWHM (nm): 0.50
Substrate:  Fused Silica (Coming 7980)
Minimum Transmission (%): >70
Coating: Hard Coated
Transmission (%): T _{abs} >70% @ 354.78nm
Type: Bandpass Filter
Blocking Wavelength Range (nm): 200 - 335, 375 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.00 ±0.10
Note: Filter Design: Single Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant