

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

355nm Flat Top Beam Shaper | πShaper 12_12_355_HP

See More by [AdiOptica](#)



Stock #15-497 [CONTACT US](#)



1



€9.584,00

ADD TO CART

Qty 1-4

€9.584,00

Qty 5+

€8.626,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
355

Diameter (mm):
42.00

Entrance Beam Diameter, 1/e² (mm):
12.0 - 12.1

Model Number: πShaper 12_12_355_HP
Length (mm): 358.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <530
Wavelength Range (nm): 330 - 380
Style: Flat Top
Damage Threshold, By Design: ☐ 3 J/cm² @ 5ns (typical)
Output Diameter, FWHM (mm): 11.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant