

40° Diffusing Angle 12.5mm Unmounted



Stock **#35-868** 3-4 DAYS

-

1

+

€90,00

ADD TO CART

Qty 1-5
€90,00
Qty 6+
€67,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°): ±4
Diffusing Angle (°): 40 (FWHM)
Diameter (mm): 12.50
Dimensional Tolerance (mm):

±0.5
Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
