

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



35mm Fixed Focal Length, #14-400

Stock #14-400 3-4 DAYS



1



€315,00

ADD TO CART

Qty 1+

€315,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:  
Variable

Length (mm):  
36.91

Horizontal Field of View, 1/2" Sensor:  
10.5°

Horizontal Field of View, 2/3" Sensor:  
14.4°

Filter Thread:

|                                                               |
|---------------------------------------------------------------|
| M30.5 x0.50 (Female)                                          |
| <b>Maximum Diameter (mm):</b><br>32.5                         |
| <b>Weight (g):</b><br>90                                      |
| <b>Horizontal Field of View, 1/3" Sensor:</b><br>8°           |
| <b>Maximum Image Circle (mm):</b><br>11.00                    |
| <b>Horizontal Field of View @ Max Sensor Format:</b><br>14.4° |
| <b>Type:</b><br>Fixed Focal Length Lens                       |
| <b>Focal Length FL (mm):</b><br>35.00                         |
| <b>Maximum Sensor Format:</b><br>2/3"                         |
| <b>Working Distance (mm):</b><br>500 - ∞                      |
| <b>Mount:</b><br>C-Mount                                      |
| <b>Aperture (f/#):</b><br>f/1.4 - f/32                        |
| <b>Distortion (%):</b><br><-1                                 |
| <b>Horizontal Field of View, 1/4" Sensor:</b><br>5.23°        |
| <b>Lens Wavelength Range:</b><br>VIS                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |