

35mm Dia. x 15mm FL Protected Gold, Concave Mirror



Stock **#43-837** [CONTACT US](#)

⊖ 1 ⊕ **€61,00**

ADD TO CART

Qty 1-49
€61,00
Qty 50+
€52,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: [N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):

35.00 ±0.50
Effective Focal Length EFL (mm): 15.00
Radius of Curvature (mm): 30.00
Aperture (f/#): f/0.43
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.0
Radius R₁ (mm): 30.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 700 - 10000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
