

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

35mm Dia. X 35mm FL Protected Aluminum, Concave Mirror



Stock #43-468 3-4 DAYS

- 1 + €50,50

ADD TO CART

Qty 1-49

€50,50

Qty 50+

€43,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐
[N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):

35.00 ±0.50
Effective Focal Length EFL (mm): 35.00
Radius of Curvature (mm): 70.00
Aperture (f/#): f/1
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.0
Radius R₁ (mm): 70.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant