

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

35mm Diameter X 26.2mm FL, MgF₂ Coated, Aspheric Condenser Lens



Stock #15-537 3-4 DAYS

[Other Coating Options](#)



1



€66,00

ADD TO CART

Qty 1-10

€66,00

Qty 11+

€59,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
35.00 +0.0/-0.4

Effective Focal Length EFL (mm):
29.00

Numerical Aperture NA:
0.61

Back Focal Length BFL (mm): 16.30
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤25
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 29.1
Edge Thickness ET (mm): 4.0
Center Thickness CT (mm): 13.90 ±0.25
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 31.1
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant