

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 35mm, 1/8" CI Series Fixed Focal Length Lens



35mm Focal Length

Stock #85-367 ■ In Stock



1



€215,00

ADD TO CART

Qty 1+

€215,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
41.00

Horizontal Field of View, 1/2" Sensor:
16.1mm - 10.4°

Horizontal Field of View, 2/3" Sensor:
22.1mm - 14.3°

Filter Thread:

M30.5 x0.50 with required adapter #89-942
Maximum Diameter (mm): 26.5
Weight (g): 45
Horizontal Field of View, 1/3" Sensor: 12.0mm - 7.8°
Maximum Rear Protrusion (mm): 0.18
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.018
Horizontal Field of View @ Max Sensor Format: 22.1mm - 14.3°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 18.1mm - 11.7°
Front Thread: M25.5 x0.5 (Male)
Horizontal Field of View, 1/2.5" Sensor: 14.6mm - 9.4°
Type: Fixed Focal Length Lens
Diameter (mm): 26.50
Focal Length FL (mm): 35.00
Primary Magnification PMAG: 0.4
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/8
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 21.27
Horizontal Field of View, 1/4" Sensor: 9.0mm - 5.9°
Object Space Principal Plane (mm): 22.42
Image Space Principal Plane (mm): -20.67
Field of View at Max Sensor Format: Horizontal: 22.1mm - 14.3° Vertical: 16.6mm - 10.7° Diagonal: 27.7mm - 17.8°
Maximum Distortion (%): 0.17
Exit Pupil Position (mm): -21.87
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View

