


36" L x 24" W, Resolving Power Chart



Stock **#83-001** 20+ In Stock

-

1

+

€55^{.50}

ADD TO CART

Volume Pricing	
Qty 1-4	€55,50 each
Qty 5+	€53,50 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Do to the nature of the printing process, maximum resolvable resolution is an only an estimate.

Physical & Mechanical Properties

36.00

Length (inches):

24.00

Width (inches):

Optical Properties

White Poster Paper

Substrate:

Minimum: Group -2, Element 1
Maximum Estimated: Group 2, Element 1

Resolution:

Regulatory Compliance

View

Certificate of Conformance:

Product Details

- Test for Astigmatism
 - USAF Test Pattern in Black, Red, Yellow, and Blue
 - 6 Elements in 6 Groups
- USAF pattern is printed in black, red, yellow, and blue to test for chromatic aberration and at 90° for testing astigmatism.

Technical Information

Element	Group No.					
	-2	-1	0	1	2	3
1	0.250	0.500	1.00	2.00	4.00	8.00
2	0.280	0.561	1.12	2.24	4.49	8.98
3	0.315	0.630	1.26	2.52	5.04	10.10
4	0.353	0.707	1.41	2.83	5.66	11.30
5	0.397	0.793	1.59	3.17	6.35	12.70
6	0.445	0.891	1.78	3.56	7.13	14.30