

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #67-895 3-4 DAYS

-

1

+

 €486,00

ADD TO CART

Qty 1-9

€486,00

Qty 10+

€436,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
50.00 +0.00/-0.25

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

|                                                           |
|-----------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>45.0                    |
| <b>Center Wavelength CWL (nm):</b><br>370.00 +3.0/-0.0    |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>+3.0/-0.0 |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00 ±2         |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±2     |
| <b>Minimum Transmission (%):</b><br>>25                   |
| <b>Operating Temperature (°C):</b><br>-50 to +50          |
| <b>Coating:</b><br>Traditional Coated                     |
| <b>Surface Quality:</b><br>80-50                          |
| <b>Type:</b><br>Bandpass Filter                           |
| <b>Typical Applications:</b><br>General Filtering         |
| <b>Blocking Wavelength Range (nm):</b><br>200 - 10000     |
| <b>Construction:</b><br>Mounted in Black Anodized Ring    |
| <b>Mount Thickness (mm):</b><br>5.4                       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |