

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



TECHSPEC® Yb:YAG Laser Line Mirrors

Stock #11-307 3-4 DAYS



1



€194,00

ADD TO CART

Qty 1-5

€194,00

Qty 6+

€175,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) : 90
Back Surface: Commercial Polish
Reflection at DWL (%) : 99.8
Coating Specification: R _{abs} >99.8% @ 1030nm
Wavelength Range (nm) : 1020 - 1040
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1030nm)
Design Wavelength DWL (nm) : 1030
Diameter (mm) : 38.10 +0.00/-0.10
Thickness (mm) : 6.35 ±0.20
Angle of Incidence (°) : 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, By Design: ☐ 15 J/cm² @ 1030nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View