

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

38.1mm Dia., Gold Coated, Aluminum Substrate Mirror



Metal Substrate Mirrors

Stock #47-116 [CONTACT US](#)



1



€352,00

ADD TO CART

Qty 1-5

€352,00

Qty 6+

€316,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
38.10 +0.00/-0.38

Substrate: ☐
Aluminum 6061-T6

Surface Quality:
80-50

Coating Specification: R_{avg} >94% @ 700 - 800nm R_{avg} >97% @ 800 - 2000nm R_{avg} >98% @ 2 - 12μm
Coating: Protected Gold (700-12000nm)
Coating Type: Metal
Clear Aperture (%): 90
Mounting Threads: 6-32 TPI Tapped Holes
Surface Roughness (Angstroms): <175
Thickness (mm): 9.50
Type: Flat Mirror
Wavelength Range (μm): 0.7 - 12
Wavelength Range (nm): 700 - 12000
Surface Flatness (RMS): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
