

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [ISP Optics](#)



Stock #24-835 3-4 DAYS



1



€556,00

ADD TO CART

Qty 1-5

€556,00

Qty 6+

€444,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
38.10 +0.00/-0.13

Effective Focal Length EFL (mm):
127.00 @ 10.6µm

Substrate: Germanium (Ge)
f/#: 3.33
Numerical Aperture NA: 0.15
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Center Thickness CT (mm): 4.50 ±0.20
Centering (arcmin): <3
Clear Aperture (%) : 90
Clear Aperture CA (mm): 34.29
Edge Thickness ET (mm): 4.00
Focal Length Tolerance (%) : ±2
Model Number: GE-PM-38-127
Radius R₁ (mm): 187.07
Radius R₂ (mm): 127.35
Surface Quality: 60-40
Irregularity (P-V) @ 10.6µm: λ/20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View