

[See all 4 Products in Family](#)

3mm Dia. x 12mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-060 CLEARANCE **1 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ €20⁵⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | €20,50 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

3.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

Center Thickness CT (mm):

1.50

Edge Thickness ET (mm):

1.32

Clear Aperture CA (mm):

≥2.55

Optical Properties

Effective Focal Length EFL (mm):

12.00

Back Focal Length BFL (mm):

11.01

Coating:

Uncoated

Substrate: □

[N-BK7](#)

Focal Length Tolerance (%):

±1

Radius R_1 (mm):

6.20

f#:

4.00

Numerical Aperture NA:

0.13

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Feature Standard Designs and Specifications
- Also Available with [MgF₂ Coating](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. Commercial Grade Uncoated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information

