

TECHSPEC® 3" Dia. Protected Aluminum, λ /20 Flat Fused Silica



Stock **#47-573-522** ☐ In Stock



1



€540,00

ADD TO CART

Qty 1-10

€540,00

Qty 11+

€486,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /20 (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 76.20 +0.0/-1.02
Diameter Tolerance (inches): +0.0/-0.04
Substrate: Fused Silica (Corning 7980)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Clear Aperture CA (mm): 68.58
Note: Flatness is specified as Peak to Valley
Thickness (mm): 19.10 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference: 0.3 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant