

# 3" x 3" 0.25mm Dot, Low Reflect Grid Distortion Target



Stock #62-953 3-4 DAYS

⊖ 1 ⊕ **€783,00**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| €783,00 |

|         |
|---------|
| Qty 5+  |
| €744,30 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:  
Low Reflective Chrome

Dot Diameter (mm):  
0.25

Dot Spacing (mm):  
0.5

Substrate:

|                                                        |
|--------------------------------------------------------|
| Float Glass                                            |
| <b>Pattern Size (mm):</b><br>50 x 50                   |
| <b>Dimensions (inches):</b><br>3 x 3 ±0.04             |
| <b>Thickness (mm):</b><br>2.00 ±0.2                    |
| <b>Center to Center Spacing Tolerance (µm):</b><br>± 1 |
| <b>Dot Diameter Tolerance (µm):</b><br>±3              |
| <b>NIST Certification:</b><br>No                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |