

## 40 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock #38-260 CLEARANCE **3 In Stock**

€211.<sup>00</sup>

ADD TO CART

#### Volume Pricing

Qty 1-4	€211,00 each
Qty 5+	€200,90 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

#### Product Downloads

#### Physical & Mechanical Properties

Length (inches):  
3.00

Pattern Size (mm):  
12.7 x 25.4

Thickness (mm):  
1.10

Width (inches):  
1.00

## Optical Properties

Vacuum Deposited Chrome **Coating:**

40.00 **Frequency (lp/mm):**

Float Glass **Substrate:**

3.00 **Optical Density OD (Average):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.