

40 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock #59-547 **2 In Stock**

- 1 + €322.⁰⁰

ADD TO CART

Volume Pricing

Qty 1-4	€322,00 each
Qty 5+	€306,30 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Pattern Location is Centered

Note:

No

NIST Certification:

Physical & Mechanical Properties

±0.100 **Dimensional Tolerance (inches):**

25.40	Length (mm):
12.7 x 25.4	Pattern Size (mm):
1.52 ±0.100	Thickness (mm):
76.20	Width (mm):
±0.001	Line Width Tolerance (µm):

Optical Properties

Vacuum Deposited Chrome	Coating:
40.00	Frequency (lp/mm):
Opal Glass	Substrate: <input type="checkbox"/>
>3.0	Optical Density OD (Average):
40-20	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance