

4.0 OD M77 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-416 3-4 DAYS

- 1 + **€243,00**

ADD TO CART

Qty 1-9
€243,00

Qty 10+
€230,50

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
73.00

Filter Thread:
M77 x0.75

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
