

TECHSPEC® 400-700nm OD 0.9, M25.5 x 0.5 Absorptive ND Filter



Stock **#66-707** 3-4 DAYS

⊖ 1 ⊕ **€78,00**

ADD TO CART

Qty 1-9
€78,00
Qty 10+
€72,80
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
28.00

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
22.0

Filter Thread:

M25.5 x 0.50
Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 12.50
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #46-215
Mount Thickness (mm): 9.9
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View