

TECHSPEC® 40mm, 106mm Radius, Metric Goniometer



TECHSPEC® Goniometers



Stock #66-531 ☐ In Stock

-

1

+

 €566,00

ADD TO CART

Qty 1-2

€566,00

Qty 3+

€496,20

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: Metric
Stage Size (mm): 40 x40
Travel (°): ±7.5
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Radius R (mm): 106
Resolution (arcmin): 10
Stage Size (inches): 1.57 x 1.57
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant