

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 40mm, 82mm Radius, English Goniometer



TECHSPEC® Goniometers



Stock #66-527 3-4 DAYS

- 1 +

€527,00

ADD TO CART

Qty 1-2

€527,00

Qty 3+

€459,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type: English
Stage Size (mm): 40 x40
Travel (°): ±10
Construction: Brass Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 3
Mounting Threads: (1) ¼-20, (4) 6-32, (8) 2-56
Radius R (mm): 82
Resolution (arcmin): 5
Stage Size (inches): 1.57 x 1.57
Weight (kg): 0.3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant