

**TECHSPEC** 40mm, Center Drive, Standard Top, English Micrometer Stage



Stock #66-403 **3 In Stock**

⊖ 1 ⊕ €438<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-2	€438,00 each
Qty 3+	€382,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

English **Type:**

**Physical & Mechanical Properties**

Linear (X) **Type of Movement:**

Crossed Roller Bearing **Guide System:**



**30mm Standard-Top Stages - Center Drive**




**30mm Standard-Top Stages - Side Drive**




**40mm Standard-Top Stages - Center Drive**




**40mm Standard-Top Stages - Side Drive**




**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

