

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

LENS



TECHSPEC® Precision Aspheric Lenses

Stock **#16-966-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€530,00

ADD TO CART

Qty 1-5

€530,00

Qty 6+

€424,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
40.00 ±0.025

Effective Focal Length EFL (mm):

40.00 @ 587.6nm
Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 31.21
Substrate: NSF5
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: VIS-EXT+ (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 39.00
Edge Thickness ET (mm): 6.83
Center Thickness CT (mm): 14.70 ±0.10
f#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View