

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

LENS



TECHSPEC® Precision Aspheric Lenses

Stock **#16-967-INK** [CONTACT US](#)

[Other Coating Options](#)



1



€545,00

ADD TO CART

Qty 1-5

€545,00

Qty 6+

€436,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

40.00 ±0.025

Effective Focal Length EFL (mm):

30.00 @ 587.6nm
Numerical Aperture NA: 0.66
Back Focal Length BFL (mm): 18.04
Substrate: NSF5
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: VIS-EXT+ (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm @ ±30° AOI R _{abs} <1.5% @ 350 - 700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 36.00
Edge Thickness ET (mm): 8.83
Center Thickness CT (mm): 20.00 ±0.10
f#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View