

TECHSPEC[®] 4.0mm Diameter x 8.0mm Length, N-BK7 Rod Lens



Stock #54-089 14 In Stock

-

1

+

€50^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	€50,00 each
Qty 6-25	€40,00 each
Qty 26-49	€38,00 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Rod Lens

Type:

Physical & Mechanical Properties

4.00 +0.00/-0.03

Diameter (mm):

8.00

Length (mm):

Length Tolerance (mm):	
+0/-0.1	
Optical Properties	
N-BK7	Substrate: ☐
	Coating:
Uncoated	
Wavelength Range (nm):	
350 - 2200	
Surface Quality:	
40-20	
Regulatory Compliance	
Compliant	RoHS 2015:
	Reach 219:
Compliant	
Certificate of Conformance:	
View	

Product Details

- Focuses Collimated Light into a Line
- Available in Diameters as Small as 1mm

TECHSPEC® Rod Lenses are polished on the circumference and ground on both ends. Optical performance is similar to a cylinder lens. Collimated light passing through the diameter of the rod lens will be focused into a line. TECHSPEC ® Rod Lenses are offered in diameters ranging from 1mm to 10mm.

Technical Information

Rod Lens

