

TECHSPEC 40mm Length, C-Mount Extension Tube



Stock #54-631 **20+ In Stock**

⊖ 1 ⊕ €52.⁵⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€52,50 each
Qty 5-9	€46,60 each
Qty 10-25	€43,10 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Extension Tube **Type:**
Extension Tube (Fixed) **Function:**

Physical & Mechanical Properties

40.0 **Extension Length (mm):**

44.0 Total Length (mm):

22.0 Clear Aperture CA (mm):

30.0 Outer Diameter (mm):

Threading & Mounting

C-Mount Thread Type:

Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

