

40mm Travel, X-Z Two Axis Precision Movement



#03-600

Stock **#03-600** 3-4 DAYS



1



€386,00

ADD TO CART

Qty 1-9

€386,00

Qty 10+

€340,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X-Z)

Guide System:
Dovetail

Type of Drive:
Rack and Pinion

Type: English
Stage Size (mm): 20 x 125
Travel (mm): 40 (±20)
Load Capacity (kg): 3.5 Horizontal, 2.1 Vertical
Mounting Threads: Stage: (1) ¼-20 Base: (2) 8-32
Note: Not Lockable
Straight Line Accuracy (µm): 50
Travel Per Knob Rotation (mm): 15
Weight (g): 485
Table Size (mm): 20 x 60

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View