

40X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)

See More by [Nikon](#)



40X Objective, Nikon CFI Plan Fluor, #88-381

Stock #88-381 3-4 DAYS

$\ominus$ 1 $\oplus$

€2.189,00

ADD TO CART

Qty 1+

€2.189,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
0.63

Horizontal Field of View, 1/2" Sensor:
0.16mm

Horizontal Field of View, 2/3" Sensor:
0.22mm

Model Number: MRH00401
Length excluding Threads (mm): 59.20
Magnification: 40X
Maximum Diameter (mm): 30
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.75
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 0.66
Weight (g): 242.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 25.2
Parfocal Length (mm): 59.86
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)