

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 4.25" Diameter X 17.5" FL Enhanced Aluminum, Parabolic Mirror



Stock #32-065-533 [CONTACT US](#)



1



€486,00

ADD TO CART

Qty 1-9

€486,00

Qty 10+

€413,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®

Focal Length Tolerance (%): ±1

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 4.25 +0.02/-0
Diameter (mm): 108.00 +0.5/-0
Effective Focal Length EFL (inches): 17.5
Effective Focal Length EFL (mm): 444.50
Radius of Curvature (mm): 889.00
Aperture (f/#): f/4.1
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (μm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant