

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 4.25" Diameter X 34" FL Protected Aluminum, Parabolic Mirror



Stock #32-067-522 [CONTACT US](#)



1



€436,00

ADD TO CART

Qty 1-9

€436,00

Qty 10+

€371,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate:

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:

N/8
Diameter (inches): 4.25 +0.06/-0
Diameter (mm): 108.00 +1.5/-0
Effective Focal Length EFL (inches): 34.0
Effective Focal Length EFL (mm): 863.60
Radius of Curvature (mm): 1,727.20
Aperture (f/#): f/8
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 98
Edge Thickness ET (inches): 0.75
Edge Thickness ET (mm): 19.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.4 - 2
Wavelength Range (nm): 400 - 2000
Damage Threshold, Reference:  0.3 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant