

4.25µm 25mm Diameter, IR Shortpass Filter



Stock #21-255 3-4 DAYS

- 1 + **€450,00**

ADD TO CART

Qty 1-5
€450,00

Qty 6+
€405,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Angle of Incidence (°):
0

Optical Density OD (Average):
≥3.0

Cut-Off Wavelength (nm): 4,250.00
Cut-Off Wavelength (μm): 4.25
Substrate:  Silicon
Rejection Wavelength (nm): 4510 - 7000
Surface Quality: 80-50
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.2
Transmission (%): ≥85
Transmission Wavelength (nm): 3300 - 4150
Transmission Wavelength (μm): 3.3 - 4.15
Type: Shortpass Filter
Durability: ML-C-48497A, Section 4.5.3
Cut-Off Tolerance (%): ±2
Rejection Wavelength (μm): 4.51 - 7

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
