

4.4-11mm FL High Resolution Varifocal Lens



#68-665

Stock **#68-665** 4 In Stock

-

1

+

€581⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€581,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Low Distortion	Note:
Varifocal Lens	Type:
Physical & Mechanical Properties	
56.50	Length (mm):
	Weight (g):

125.00	
45.00	Diameter (mm):
Optical Properties	
400 - 175	Field of View @ Min Working Distance (mm):
68.1° - 32.6°	Horizontal Field of View, 1/2" Sensor:
4.4-11	Focal Length Range (mm):
300 - ∞	Working Distance (mm):
f/1.6 - f/16	Aperture (f/#):
VIS	Lens Wavelength Range:
Sensor	
1/1.8"	Maximum Sensor Format:
Threading & Mounting	
M43 x0.75	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.