

450 - 600nm, λ/4 Polymer Achromatic Waveplate



Polymer Waveplates (Retarders)

Stock **#88-198** ☐ In Stock

⊖ 1 ⊕ **€431,00**

ADD TO CART

Qty 1-5
€431,00

Qty 6+
€345,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
R_{avg} <0.5% @ 400 - 700nm

Diameter (mm):
25.00

Substrate: ☐
[B270](#)

Retardance: λ/4
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Polymer Achromatic Waveplate
Parallelism (arcmin): 3.00
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Birefringent Polymer Stack
Retardance Tolerance (nm): ±10 @ 450 - 600
Wavelength Range (nm): 450 - 600
Retardance Order: Achromatic

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
