

TECHSPEC®

45° Hot Mirror Mounted in C-Mount Cube



Stock **#62-641** 3-4 DAYS

-

1

+

€280,00

ADD TO CART

Qty 1+

€280,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
80-50

Type:
Hot Mirror

Extension Length (mm):
38.0

Dimensional Tolerance (mm):
0.5

Type of Optics:
45° Hot Mrror

Coating Specification:
T_{avg} ≥85% @ 425 - 675nm
R_{avg} ≥90% @ 750 - 1125nm

Thread Type:
C-Mount (1" x 32 TPI)

Coating:
Hot Mirror, 45°

Substrate: ☐
[BOROFLOAT®](#)

Filter Included:
[#62-630](#)

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)