

TECHSPEC® 4.5mm f/11 Sealed Cw Series Fixed Focal Length Lens



4.5mm Focal Length



Stock **#15-618** 3-4 DAYS



1



€485,00

ADD TO CART

Qty 1+

€485,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
40.82

Horizontal Field of View, 1/2" Sensor:
76.8°

Filter Thread:

M49 x 0.75 (Female)
Maximum Diameter (mm): 54.00
Horizontal Field of View, 1/3" Sensor: 59.34°
Maximum Rear Protrusion (mm): 3.3
Maximum Image Circle (mm): 9.00
Numerical Aperture NA, Object Side: 0.0050
Number of Elements (Groups): 9 (8)
Note: C-Mount compatible with O-ring 25mm ID x 2mm
Horizontal Field of View, 1/1.8" Sensor: 84.7°
Horizontal Field of View, 1/2.5" Sensor: 70.1°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 4.50
Primary Magnification PMAG: 0.109
Maximum Sensor Format: 1/1.8"
Working Distance (mm): 75 - ∞
Mount: C-Mount
Aperture (f/#): f/11
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 27.308
Object Space Principal Plane (mm): -31.12
Image Space Principal Plane (mm): 35.70
Field of View at Max Sensor Format: Horizontal: 84.7° Vertical: 66.1° Diagonal: 100.0°
Maximum Distortion (%): 15.959
Exit Pupil Position (mm): -9.272
Environmental Rating: IPX7
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View