

4mm - 12mm Focal Length, Varifocal Video Lens



Varifocal Imaging Lenses



Stock **#58-365** ☐ In Stock

- 1 +

€230,00

ADD TO CART

Qty 1+

€230,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
639 - 168

Length (mm):
50.30

Horizontal Field of View, 1/2" Sensor:
93.6° - 31.2°

Maximum Diameter (mm):

40.0
Maximum Rear Protrusion (mm): 4.6
Type: Varifocal Lens
Focal Length FL (mm): 4.00 - 12
Maximum Sensor Format: 1/2"
Working Distance (mm): 300 - ∞
Mount: C-Mount
Aperture (f/#): f/1.2 - f/16
Lens Wavelength Range: VS

Regulatory Compliance

Reach 174: Compliant
RoHS: Compliant
Certificate of Conformance: View