

4μm λ/2 MWIR Zero Order Waveplate



Stock #85-118 3-4 DAYS

⊖ 1 ⊕ **€930,00**

ADD TO CART

Qty 1-9
€930,00

Qty 10+
€845,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
10.0

Design Wavelength DWL (nm):
4000

Diameter (mm):
25.40

Substrate:

MgF ₂
Retardance: λ/2
Type: Crystalline Waveplate
Parallelism (arcmin): 3
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/8 @ 632.8nm
Retardance Tolerance: λ/100 @ 20°C
Mount Thickness (mm): 6.0
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant