

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



65mm WD, 4X, In-Line Version (Left) and VIS Version (Right)

Stock #63-736 ■ In Stock



1



€635,00

ADD TO CART

Qty 1+

€635,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length excluding Threads (mm):
81.00

Horizontal Field of View, 1/2" Sensor:
1.6mm

Horizontal Field of View, 2/3" Sensor:
2.2mm

Filter Thread:
M25.5 x 0.50 (Female) with Required Adapter [#88-212](#)
Sold Separately

Maximum Diameter (mm): 18.00
Weight (g): 50
Horizontal Field of View, 1/3" Sensor: 1.2mm
Numerical Aperture NA, Object Side: 0.074
Working Distance Tolerance (mm): ±1
Number of Elements (Groups): 5 (3)
Note: CompactTL™
Typical Telecentricity @ 588nm (°): 0.008
Typical Distortion @ 588nm (%): 0.0071
Front Thread: M16 x 0.5 (Female)
Manufacturer: Edmund Optics®
Type: Telecentric Lens
Primary Magnification PMAG: 4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65
Mount: C-Mount
Aperture (f/#): f/26.3
Coating: λ/4 MgF ₂
Depth of Field (mm): ±0.09mm (20% @ 20 lp/mm)
FOV @ Max Sensor Format, H x V (mm): 2.2 x 1.6
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View