

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 4X, UV-VIS Vega® Broadband Beam Expander



TECHSPEC® Vega™ Broadband Beam Expanders

Stock #19-405 3-4 DAYS



1



€449,00

ADD TO CART

Qty 1+

€449,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Coating:

Laser UV-VIS (250-532nm)

Design Wavelength DWL (nm):

Broadband

Entrance Aperture (mm):

7.5

Exit Aperture (mm): 26
Expansion Power: 4X
Substrate: ☐ Fused Silica
Length (mm): 67.00 - 79.00
Mounting Threads: Input: Male M30 x 1 Output: Female M34 x 0.5
Transmission (%): >95.0 (nominal)
Type: Beam Expander
Weight (g): 160
Housing Diameter (mm): 39.95
Transmitted Wavefront, P-V: λ/10 for 4.0mm input beam (nominal, λ = DWL)
Coating Specification: Ravg ≤1.25% @ 250 - 532nm @ 0° AOI
Wavelength Range (nm): 250 - 532
Style: Fixed Magnification
Damage Threshold, By Design: ☐ 1 J/cm² @ 532nm, 20ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View