

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Bar Lights](#) / [Effilux Adjustable LED Bar Lights](#)

[See all 21 Products in Family](#)

## 5 LED, Red Adjustable LED Bar Light

## 5 LED, Red Adjustable LED Bar Light



Stock #34-876 3-4 DAYS

$\ominus$     1     $\oplus$

**€570,00**

**ADD TO CART**

Qty 1+

**€570,00**

## Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

## Get Product Downloads

**Color:**  
Red

**Connector:**  
M12, 5 pins

**Input Voltage (V):**  
24VDC

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Model Number:</b><br>EFFI-FLEX-5-625                                                                                                                                                                                                     |
| <b>Mount:</b><br>2 Rails (1 for M6 T-Nuts)                                                                                                                                                                                                  |
| <b>Operating Temperature (°C):</b><br>-10 to 50                                                                                                                                                                                             |
| <b>Dimensions (mm):</b><br>135.0 x 51.0 x 49.0                                                                                                                                                                                              |
| <b>Wavelength (nm):</b><br>625.00                                                                                                                                                                                                           |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#15-874</a><br>Europe: <a href="#">#15-875</a><br>Japan: <a href="#">#15-874</a><br>Korea: <a href="#">#15-874</a><br>China: <a href="#">#15-874</a> |
| <b>Number of LEDs:</b><br>5.00                                                                                                                                                                                                              |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Geometry:</b><br>Line Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Strobed or Constant                                                                                                                                                                                            |
| <b>Environmental Rating:</b><br>IP40                                                                                                                                                                                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |