

## 5 x 30° Diffusing Angle 2" x 2" Unmounted



Stock #48-007 3-4 DAYS

⊖ 1 ⊕ **€242,50**

**ADD TO CART**

Qty 1-5

€242,50

Qty 6+

€206,25

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Angle Tolerance (°):**

±1 x ±3

**Diffusing Angle (°):**

5 x 30 (FWHM)

**Dimensional Tolerance (mm):**

±0.5

**Dimensions (inches):**  
2 x 2

**Dimensions (mm):**  
50.80 x 50.80

**Operating Temperature (°C):**  
-30 to +100 (Maximum of 240 Hours)

**Substrate:**   
Polycarbonate

**Thickness (mm):**  
0.78

**Transmission (%):**  
>85

**Type:**  
Holographic Diffuser

**Wavelength Range (nm):**  
400 - 700

**Width (mm):**  
50.80

**Construction:**  
Unmounted

**Damage Threshold, By Design:**   
0.22 J/cm<sup>2</sup> @ 1064nm, 10ns (typical)

**Length (mm):**  
50.80

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Compliant](#)

---