

TECHSPEC® 5 x 5mm Enhanced Aluminum, λ/4 Mirror



Stock **#48-405** ☒ In Stock

1 **€50,00**

ADD TO CART

Qty 1-5
€50,00

Qty 6+
€40,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT®](#)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Dimensions (mm): 5.0 x 5.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 83
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Length (mm): 5.00
Width (mm): 5.00
Damage Threshold, Reference: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant