

5.0" White, LED Darkfield Illuminator

See More by [Advanced Illumination](#)



Stock #66-792 3-4 DAYS

⊖ 1 ⊕

€861,00

ADD TO CART

Qty 1+

€861,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Height (mm):
46.2

Inner Diameter (mm):
55.0

Model Number:

RL3536B-WH-IC
Mount: Standard and Barrel Mount
Operating Temperature (°C): 0 to +65
Outer Diameter (mm): 127.0
Mounting Threads: M4 x4
Working Distance (mm): 75 - 100
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of LEDs: 36.00
Number of Channels: 1.00
Field Coverage (mm): 32 - 38
Maximum Trigger Frequency (Hz): 30.00
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)